



Line laser

GLL 2-50 Professional



GLL 2-50 Professional



- Vertical, horizontal, and cross line modes for precise alignment
- Easy handling due to single-handed operation
- Horizontal and vertical self-levelling up to $\pm 4^\circ$
- Working range of 50 m with the Receiver LR 2 Professional (optional)
- Robust design with softgrip covering protects against knocks
- Pendulum lock ensures safe transport

Part no. 0 601 063 100

- Protective pouch (1 609 203 X77)
- Alignment disc (ET no. 1 609 203 U23)
- 3 x 1.5 V batteries

Part no. 0 601 063 101

- BS 150 Professional Building Tripod (0 601 096 974)
- Protective pouch (1 609 203 X77)
- Alignment disc (ET no. 1 609 203 U23)
- 3 x 1.5 V batteries

Part no. 0 601 063 102

- BM 1 Professional Universal Mount (0 601 015 A00)
- Carrying case
- Alignment disc (ET no. 1 609 203 U23)
- 3 x 1.5 V batteries

Part no. 0 601 063 103

- LR 2 Professional Laser Receiver (0 601 069 100)
- BM 1 Professional Universal Mount (0 601 015 A00)

- Carrying case
- 3 x 1.5 V batteries
- 1 x 9 V battery
- Alignment disc (ET no. 1 609 203 U23)

Technical data

Laser diode	635 nm, < 1 mW
Operating temperature	-20 – 50 °C
Storage temperature	-20 – 70 °C
Laser class	2
Working range	20 m
Working range with receiver	50 m
Levelling accuracy	± 0.3 mm/m
Self-levelling range	± 4°
Dust and splash protection	IP 54
Power supply	3 x 1.5 V LR6 (AA)
Operating time, max.	12 h
Tripod connection	1/4"
Weight	0,45 kg
Length	118 mm
Width	57 mm
Height	89 mm

