

Product Information



LEVINA 5377PJP150P30-13

Swivel castor with total lock, tail end of castor, housing and wheels made from high grade synthetic materials, double ball bearing swivel head. Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, precision ball bearing, bolt hole

Technical Data	
Wheel diameter	150 mm
Width of Tread	32 mm
Centre hole	13 mm
Offset	38 mm
Swivel Interference	240 mm
Overall height	190 mm
Temperature	- 10 / + 40 °C
Standard	EN 12530
Load capacity	100 kg
Load capacity (static)	200 kg
Hardness of tread	A 87 Shore



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+



Product Information



LEVINA 5377PJP150P30-13

