

FatMax



FatMax® Pozi Insulated

- ➔ Individually tested to 10,000 volts
- ➔ Large diameter handle offers great torque needed for driving wood screws
- ➔ Extremely tough Polyamide blade insulation sleeve makes it resistant to impact at -25 degrees centigrade and ensures increased abrasion resistance and reduced moisture absorption
- ➔ The Ergonomic handle design offers both a large diameter for increased torque and a small diameter shaft ensuring high speed fastening/unfastening of machine screws - The soft touch grip ensures increased grip and comfort
- ➔ An industrial grade - 1000V a.c. insulation - Tested to EN60900:2004 meaning that that this screwdriver is suitable for live working use up to 1000V a.c
- ➔ Colour coded ends make it easy to identify the correct screwdriver for each screw type
- ➔ Smooth domed end for fast spinning action – speed and comfort
- ➔ Shot blasted tips ensure improved torque and corrosion protection
- ➔ Soft grip handle – perfect combination of great grip plus reduces fatigue
- ➔ Chrome vanadium steel bar allows for high torque and reduces the chance of tip breakage
- ➔ Handle moulded direct to bar virtually unbreakable bond. Highly reliable and providing an extra long life

STANLEY	<u>65-417</u>	<u>65-418</u>	<u>65-419</u>
Pozidriv tip number	PZ0	PZ1	PZ2
Blade length (mm)	75	100	125