



World Wide [Change](#)

[Home](#) [Products](#) [Support](#) [Services](#) [Select a Store](#) [How to Buy](#)

Surge Arrest Essential

APC Essential Surge Arrest 1 outlet with Phone Protection 230V UK

P1T-UK

[Email Technical Specification](#)

[Printer Friendly](#)



Essential surge protection for computers and electronics.

Includes 1.8 Meter Tel cable (2), User Manual

Standard Lead Time Usually in Stock

[More Images](#)

[Technical Specifications](#) [Product Overview](#) [Documentation](#)

Output

Number of Outlets

1

Receptacle Style

UK BS1363 plug

Input

Nominal Input Voltage

230V

Input Frequency

50/60 Hz

Input Connections

British BS1363A

Maximum Line Current per phase

10A

Surge Protection and Filtering

Surge energy rating

960 Joules

eP Joule Rating

1060

EMI/RFI Noise rejection (100 kHz to 10 mHz)

20 dB

Peak Current Normal Mode

13 kAmps

Peak Current Common Mode

13 kAmps

Dataline protection

RJ11 Modem/Fax protection

Let Through Voltage Rating

< 900

Physical

Net Weight

0.10 KG

Maximum Height

94.00 mm

Maximum Width

70.00 mm

Maximum depth

76.00 mm

Shipping Weight

0.10 KG

Shipping Height

114.00 mm

Shipping Width

89.00 mm

Shipping Depth

83.00 mm

Master Carton Units

12.00

Master Carton Dimensions (Length x Width x Height)

13.75 X 11.12 X 5.25 inches

Master Carton Weight

3.00 lbs.

SCC Codes

1073130422392 1

Color

Charcoal

Units per Pallet

756.00

Environmental

Operating Environment

0 - 40 °C

Operating Relative Humidity

0 - 95%

Operating Elevation

0-15000 meters

Storage Temperature

-15 - 45 °C

Storage Relative Humidity

0 - 95%

Storage Elevation

0-15000 meters

Conformance

Regulatory Approvals

CE

Standard Warranty

3 years (all other countries), Lifetime (European Union countries only)

UL 1449 TVSS Rating

--V

Copyright © American Power Conversion Corp., all rights reserved

[About APC](#) [Investors](#) [Job Seekers](#) [Press](#) [Feedback](#) [Contact](#) [Privacy Policy](#)