

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOCAD

DIST00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	AM3	REVISED PER ECO-11-004587	11MAR11	RK	HMR

1. FOR ADDITIONAL SPECIFICATIONS SEE AMP PRODUCT SPEC 108-7532.

2. SWITCH SHOWN IN OPEN POSITION.

3. ALL CHARACTERS AND ROCKERS ARE WHITE, HOUSING IS BLUE.

4. STAMPING WILL VARY ON 2 AND 3 POSITION SIDES DUE TO SPACE RESTRICTIONS.

5. .315 DIMENSION APPLIES AT TERMINAL TIPS. TERMINALS ARE .300^{+.010}-.000 AT MOUNTING SURFACE.

6. STRIPPABLE TRANSPARENT SEAL, SEE FIG 1.

7	OBSOLETE	FIG 6	-----	1.08	10	6-435640-1
			-----	.58	5	6-435640-0
			-----	.48	4	5-435640-9
			-----	.88	8	5-435640-8
			-----	.98	9	5-435640-7
			-----	.68	6	5-435640-6
			-----	.58	5	5-435640-5
			-----	.48	4	5-435640-4
			-----	1.08	10	5-435640-1
			-----	.88	8	5-435640-0
			-----	.88	8	4-435640-9
			-----	.58	5	4-435640-8
			-----	1.08	10	4-435640-7
			-----	1.28	12	4-435640-3
			-----	1.08	10	4-435640-1
			-----	.98	9	4-435640-0
			-----	.88	8	3-435640-9
			-----	.78	7	3-435640-8
			-----	.68	6	3-435640-7
			-----	.58	5	3-435640-6
			-----	.48	4	3-435640-5
			-----	.38	3	3-435640-4
			-----	.28	2	3-435640-3
			-----	1.28	12	3-435640-2
			-----	.38	3	3-435640-0
			-----	.28	2	2-435640-9
			-----	.78	7	2-435640-2
			-----	1.08	10	435640-7
			-----	.98	9	435640-6
			-----	.88	8	435640-5
			-----	.68	6	435640-4
			-----	.58	5	435640-3
			-----	.48	4	435640-2
			-----	.78	7	435640-1
			-----	A	NO OF POSN	PART NO.

1 2 3 4 5 6

OFF

ROCKER DOWN

.38±.02

435640-4

AMP

XXXX

DATE CODE

.022±.002 TYP

.100 TYP

A±.02

PIN 1 IDENT DOT

.34±.02 TYP

.14±.02 TYP

.012 TYP

.19±.01

.315±.010

.02^{+.01}_{-.00} STANDOFF, 4 PLC

.29±.02 TYP

MOUNTING SURFACE

PROTECTIVE SEAL

CONTACT ARRANGEMENT

FIG 1

1 2 3 4 5 6 7

ON

OFF

FIG 2

1 2 3 4 5 6

OFF

FIG 3

1 2 3

OFF

FIG 4

1 2 3 4 5 6 7 8 9 10

OPEN

FIG 5

1 2 3 4 5 6 7 8 9

OFF/OPEN

FIG 7

1 2 3 4 5 6 7 8 9 10

ROCKER DOWN

FIG 6

7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R.TALLEY 15NOV89

CHK R.L.MILLER 06MAR90

APVD H.LEITER 06MAR90

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS: INCHES

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

FINISH

CONTACTS: PLATED .000030 MIN GOLD IN CONTACT AREA OVER .000050 MIN NICKEL

TE Connectivity

NAME

SWITCH ASSY, DIP, TYPE C, 7100 SERIES, SPST, STANDARD

SIZE A2

CAGE CODE 00779

DRAWING NO C-435640

RESTRICTED TO -

SCALE 4:1

SHEET 1 of 1

REV AM3