

End cover - D-UK 4/10 - 3003020

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




End cover, Length: 42.5 mm, Width: 1.8 mm, Height: 35.9 mm, Color: gray

Why buy this product



Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 017918 090425
Weight per Piece (excluding packing)	2.06 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

General

Color	gray
Inflammability class according to UL 94	V0

Dimensions

Width	1.8 mm
Length	42.5 mm
Height	35.9 mm

General

Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Static insulating material application in cold	-60 °C

End cover - D-UK 4/10 - 3003020

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141145
eCl@ss 5.1	27141145
eCl@ss 6.0	27141133
eCl@ss 7.0	27141133
eCl@ss 8.0	27141133

ETIM

ETIM 2.0	EC000886
ETIM 3.0	EC000886
ETIM 4.0	EC000886
ETIM 5.0	EC000886

UNSPSC

UNSPSC 6.01	30211827
UNSPSC 7.0901	39121424
UNSPSC 11	39121424
UNSPSC 12.01	39121424
UNSPSC 13.2	39121424