


Touch Side View


CONNECTOR PINOUT:

- PIN 1: Rear side ITO for EMI Shielding
PIN 2-6: Blank
PIN 7-31: Sense X1-X25
PIN 32-50: Sense Y1-Y19
PIN 51-60: Blank



NOTES:

1. INPUT MODE : PROJECTED CAPACITIVE
2. OVERALL THICKNESS : 1.75±0.20mm
3. COVER GLASS THICKNESS : 1.10mm
4. FRONT SURFACE : CLEAR TYPE
5. TAIL TYPE : GOLD PLATED FPC , ZIF
6. OTHER SPEC : SEE APPROVAL SHEET



NO.	DATE	DESCRIPTION	CHK
REVISION			
CHIEF OF DESIGN	Jerry	APPROVED	Alex
ENGINEER		PROJECT MANAGER	
DRAWN BY	Andre	DATE	Dec 27 , 2010
SHT 1	OF 1	REV.	

Apex Material Technology Corp.			
TOLERANCES UNLESS SPECIFIED		MODEL NAME : P3007	
.X	± 0.50	DWG NO : P3007-0-011	
.XX	± 0.50		
.XXX	± 0.30		
ANGULAR		SCALE: N/S UNIT: mm	