





LOC	DIST	P	F	ZONE	LTR	REVISIONS		DATE	APPD
AD	39								
					U2	REVISED PER ECO-11-005140		30MAR11	HMR

PRODUCT INSTRUCTION

PULL ON HOUSING TO REMOVE FROM POSTS.
DO NOT CONFINE THE CONDUCTORS OR PULL ON THE
CONDUCTORS DURING REMOVAL ACTION.



SEE DETAIL Z



- HOUSING ACCEPTS LOCKING CLIP CONTACT PART NO.S 87124, 87165,87190,87191,& MATES WITH .025 SQ. POSTS.
- HOUSING: GLASS FILLED NYLON.
- HOUSING: GLASS FILLED POLYESTER.
- CORE PIN SUPPORT HOLES ARE OPTIONAL, AND MAY BE ROUND OR SQUARE OR MAY NOT BE PRESENT AT ALL.
- MARKED (WHITE) AS SHOWN, THIS SIDE ONLY, WITH .06 HIGH CHARACTERS APPROX. IN CENTER OF HOUSING. "PULL HERE" AND PART NO. TO APPEAR ON HOUSINGS 6 POSITION AND LARGER.
- RAISED AMP LOGO MOLDED IN HOUSING.
- TEXTURED AMP LOGO MOLDED IN HOUSING. LOGO MAY APPEAR ON EITHER END OF HOUSING.

⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

⚠ OBSOLETE	⚠	⚠	⚠	BROWN	.058	.300	3	.416	4	6-87175-3	
SUPERSEDED BY 87175-2	⚠	⚠	⚠	YELLOW	.054	0	0	.108	1	3-87175-4	
SUPERSEDED BY 87175-2	⚠	⚠	⚠	ORANGE	.054	0	0	.108	1	3-87175-3	
SUPERSEDED BY 87175-2	⚠	⚠	⚠	RED	.054	0	0	.108	1	3-87175-2	
	⚠	⚠	⚠	BROWN	.054	0	0	.108	1	-	
⚠ OBSOLETE	⚠	⚠	⚠	BLACK	.058	1.300	13	1.416	14	3-87175-0	2-87175-9
	⚠	⚠	⚠	BLACK	.058	1.200	12	1.316	13	2-87175-8	2-87175-7
	⚠	⚠	⚠	BLACK	.058	1.100	11	1.216	12	2-87175-6	2-87175-5
	⚠	⚠	⚠	BLACK	.058	1.000	10	1.116	11	2-87175-4	2-87175-3
	⚠	⚠	⚠	BLACK	.058	.900	9	1.016	10	2-87175-2	2-87175-1
	⚠	⚠	⚠	BLACK	.058	.800	8	.916	9	2-87175-0	1-87175-9
	⚠	⚠	⚠	BLACK	.058	.700	7	.816	8	1-87175-8	1-87175-7
	⚠	⚠	⚠	BLACK	.058	.600	6	.716	7	1-87175-6	1-87175-5
	⚠	⚠	⚠	BLACK	.058	.500	5	.616	6	1-87175-4	1-87175-3
	⚠	⚠	⚠	BLACK	.058	.400	4	.516	5	1-87175-2	
	⚠	⚠	⚠	BLACK	.058	.300	3	.416	4	1-87175-0	
	⚠	⚠	⚠	BLACK	.058	.200	2	.316	3	87175-8	
	⚠	⚠	⚠	BLACK	.058	.100	1	.216	2	87175-6	
	⚠	⚠	⚠	BLACK	.058	1.400	14	1.516	15	87175-4	87175-3
	⚠	⚠	⚠	BLACK	.054	0	0	.108	1	87175-2	
NOTES	MAT'L	COLOR	D	C	B	A	POS	PART NUMBER (AS MOLDED)		PART NUMBER (STAMPED)	

				PART NO			
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 ANGLES ± 0°30' MATERIAL SEE TABLE		DR 11-16-89 D KEITZER		TE Connectivity NAME HOUSING-LOCKING CLIP .025 SQ. POST, .100 CENTERS (CLOSE END) SINGLE ROW			
		CHK 11-29-89 S. BEAM					
		APPD 11-29-89 S. BEAM					
		APPD 11-29-89 R. ELICKER					
		PRODUCT SPEC 108-36028					
FINISH -		APPLICATION SPEC 114-25006		SIZE D	FSCM NO 00779	DRAWING NO 87175	
		WEIGHT _		SCALE 4:1		SHEET 1 OF 1	