







LOC	DIST	REVISIONS			
FB	00	P	LTR	DESCRIPTION	DATE DWN APVD
		0		RELEASED FB00-0015-03	04FEB03 J. J. T. S.




SECT A-A



MATING SECTION





SECT B-B



PANEL CUTOUT DIMENSION (TOLERANCE: ± 0.1 mm)
 (RECOMMENDED PANEL THICKNESS: 0.8mm~1.6mm)


- NOTES
 1. MATERIAL
 HOUSING: 66NYLON(94V-0). COLOR: WHITE. BLUE
 POST: TIN BRASS WIRE
 2. THE PANEL SHOULD BE PUNCHED SO THAT THE HOUSING
 ENTERS THE PANEL IN THE SAME DIRECTION AS PUNCH.



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	
DIMENSIONS (mm)	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	10 $\pm$.2 30 $\pm$.10 $\pm$ 0.25 100 $\pm$.30 $\pm$ 0.3 ANGLE: $\pm 3^\circ$
MATERIAL	FINISH
SEE NOTE 1	SEE NOTE 1

DWN J. JIANG	04FEB03	tyco Electronics		Tyco Electronics Corporation Shanghai, P.R.China. 200233	
CHK S. YAO	04FEB03				
APVD T. SASAKI	04FEB03	NAME		AMP MINI COMMON TERMINATED (CT) CONNECTOR 1.5mm PITCH SINGLE ROW POST HEADER ASS'Y PANEL MOUNT TYPE	
PRODUCT SPEC 108-60018		SIZE		RESTRICTED TO	
APPLICATION SPEC 114-5223		CAGE CODE		DRAWING NO.	
WEIGHT		A3 00779		C=292215	
CUSTOMER DRAWING		SCALE		NON	
		SHEET		1 OF 2	
				REV 0	

LOC	DIST	REVISIONS						
FB	00	P	LTR	DESCRIPTION				DATE
		-	-	SEE SHEET 1				DWN
								APVD



1.41	19.8	36.5	35.9	32.5	31.7	30.6	28.5	20	7-292215-0	2-292215-0
1.35	19.8	35.0	34.4	31.0	30.2	29.1	27.0	19	6-292215-9	1-292215-9
1.30	19.8	33.5	32.9	29.5	28.7	27.6	25.5	18	6-292215-8	1-292215-8
1.24	19.8	32.0	31.4	28.0	27.2	26.1	24.0	17	6-292215-7	1-292215-7
1.19	19.8	30.5	29.9	26.5	25.7	24.6	22.5	16	6-292215-6	1-292215-6
1.13	19.8	29.0	28.4	25.0	24.2	23.1	21.0	15	6-292215-5	1-292215-5
1.08	19.8	27.5	26.9	23.5	22.7	21.6	19.5	14	6-292215-4	1-292215-4
0.97	13.1	26.0	25.4	22.0	21.2	20.1	18.0	13	6-292215-3	1-292215-3
0.92	13.1	24.5	23.9	20.5	19.7	18.6	16.5	12	6-292215-2	1-292215-2
0.86	13.1	23.0	22.4	19.0	18.2	17.1	15.0	11	6-292215-1	1-292215-1
0.81	13.1	21.5	20.9	17.5	16.7	15.6	13.5	10	6-292215-0	1-292215-0
0.75	13.1	20.0	19.4	16.0	15.2	14.1	12.0	9	5-292215-9	0-292215-9
0.64	6.4	18.5	17.9	14.5	13.7	12.6	10.5	8	5-292215-8	0-292215-8
0.59	6.4	17.0	16.4	13.0	12.2	11.1	9.0	7	5-292215-7	0-292215-7
0.53	6.4	15.5	14.9	11.5	10.7	9.6	7.5	6	5-292215-6	0-292215-6
0.48	6.4	14.0	13.4	10.0	9.2	8.1	6.0	5	5-292215-5	0-292215-5
0.44	4.9	12.5	11.9	8.5	7.7	6.6	4.5	4	5-292215-4	0-292215-4
0.37	4.1	11.0	10.4	7.0	6.2	5.1	3.0	3	5-292215-3	0-292215-3
0.30	2.6	9.5	8.9	5.5	4.7	3.6	1.5	2	5-292215-2	0-292215-2
WEIGHT (g)	G	F	E	D	C	B	A		BLUE	WHITE
DIMENSIONS								Pos	P/N	

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION ALL RIGHTS RESERVED.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

10 > : ±0.2
30 > 10 : ±0.25
100 > 30 : ±0.3
ANGLE : ±3°



DWN	
CHK	
APVD	
PRODUCT SPEC	
APPLICATION SPEC	
WEIGHT	

MATERIAL		SEE SHEET 1		FINISH		SEE SHEET 1	
tyco Electronics				Tyco Electronics Corporation Shanghai, P.R.China, 200233			
NAME AMP MINI COMMON TERMINATED (CT) CONNECTOR 1.5mm PITCH SINGLE ROW POST HDR ASS'Y PANEL MOUNT TYPE							
SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
A 4		00779		C-292215		-	
				SCALE		NON	
				SHEET		2 OF 2	
						REV 0	