

Datasheet

RS Pro Straight 75Ω Cable Mount BNC Connector Plug, Crimp Termination RG59

RS Stock No: **546-3614**



Product Details

RS Pro cable mount BNC connector plug has nickel plated body, gold plated centre contact and is suitable for RG59 cables. This 75 Ω straight BNC connector plug features bayonet coupling and crimp termination. It is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- Nickel plated body
- Gold plated centre contact
- Crimp termination method

Specifications:

Body Orientation	Straight
Body Plating	Nickel
Cable Type	Mini RG59
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	75 Ω
Mounting Type	Cable Mount
Operating Frequency	1 GHz
Polarity	Normal
Termination Method	Crimp
Contact Resistance	1.5 m Ω (Maximum Central), 0.5 m Ω (Maximum Outer)
Insulation Material	PTFE (Internal)
Insulation Resistance	5000 M Ω
Number of Functions	500
Operating Temperature Range	-65 to +85°C
Standards Met	RoHS Compliant
Voltage Rating	750 V (Insulation), 335 V (Working)