

PLC-BSC- 24DC/1/ACT

Order No.: 2966058



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2966058>

6.2 mm PLC actuator basic terminal blocks with screw connection method, input voltage 24 V DC(without relay or optocoupler)

Commercial data

EAN	4017918130817
Pack	10 Pcs.
Customs tariff	85364190
Weight/Piece	0.03029 KG

Product notes

WEEE/RoHS-compliant since:
05/04/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Input data

Nominal input voltage U_N	24 V DC
Status display	LED
Protective circuitry	Damping diode, polarity protection diode

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Type of connection	Screw connection
Stripping length	8 mm
Screw thread	M 3

General data

Length	80 mm
Width	6.2 mm
Height	94 mm
Color	green
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Operating mode	100% operating factor
Inflammability class acc. to UL 94	V0
Mounting position	Any
Assembly instructions	In rows with zero spacing

Certificates / Approvals

Approval logo



requested approvals

Certification	CUL, CUL Listed, GL, GOST, UL, UL Listed, VDE-PZI
---------------	---