

TURCK

Level Sensors - Capacitive



Housing Style	Part Number	ID Number	Features	Embeddable Range (mm)	Nonembed. Range (mm)	Output
12 mm - Embeddable, eurofast® Connector 	BC 3-M12-AN6X-0.2M-RS 4T	M2601190		3	3	3-Wire DC NPN
	BC 3-M12-AP6X-0.2M-RS 4T	M2601091		3	3	3-Wire DC PNP
12 mm - Embeddable, Potted-In Cable 	BC 3-M12-AN6X	M2601100		3	3	3-Wire DC NPN
	BC 3-M12-AP6X	M2601000		3	3	3-Wire DC PNP
12 mm - Embeddable, eurofast Connector 	BC 3-S12-AN6X-0.2M-RS 4T	M2601390		3	4.5	3-Wire DC NPN
	BC 3-S12-AP6X-0.2M-RS 4T	M2601291		3	4.5	3-Wire DC PNP
12 mm - Embeddable, Potted-In Cable 	BC 3-S12-AN6X	M2601300		3	4.5	3-Wire DC NPN
	BC 3-S12-AP6X	M2601200		3	4.5	3-Wire DC PNP
	BC 3-S12-AP6X/S100	M2601201	High Temp. 100°C	3	4.5	

Level Sensors - Capacitive

Voltage	Switching Freq. (Hz)	Operating Current (mA)	Operating Temp. (°C)	Protection Class	Housing Material	Face Material	End Cap	Power LED	Output LED	Mating Cord, Cable Length/Jacket	Wiring Diagram #	Wiring Diagrams
10-30 VDC	100	≤200	-25 to +70	IP67	CPB	ABS	PA	N/A	YE	RK 4T-*	1	Diagram 1
10-30 VDC	100	≤200	-25 to +70	IP67	CPB	ABS	PA	N/A	YE	RK 4T-*	2	Diagram 2
10-30 VDC	100	≤200	-25 to +70	IP67	CPB	ABS	PA	N/A	YE	2M/PVC	3	Diagram 3
10-30 VDC	100	≤200	-25 to +70	IP67	CPB	ABS	PA	N/A	YE	2M/PVC	4	Diagram 4
10-30 VDC	100	≤200	-25 to +70	IP67	PA 12-GF30	PA	N/A	YE	YE	RK 4T-*	1	
10-30 VDC	100	≤200	-25 to +70	IP67	PA 12-GF30	PA	N/A	YE	YE	RK 4T-*	2	
10-30 VDC	200	≤200	-25 to +70	IP67	PA 12-GF30	PA	N/A	YE	YE	2M/PVC	3	
10-30 VDC	100	≤200	-25 to +70	IP67	PA 12-GF30	PA	N/A	YE	YE	2M/PVC	4	
	100	≤200	-25 to +100	IP67	PA 12-GF30	PA	N/A	YE	YE	2M/PVC	4	

* Length in meters..