

## Ferrule - AI 1,5 - 8 BK-GB-1000 - 3202892

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Ferrule, Sleeve length: 8 mm, Length: 14 mm, Color: black




The figure shows the version AI 1,5-8

### Why buy this product

- Due to the increased diameter of the insulating collar, this type of ferrule is specifically used with AWG cables
- These ferrules enable practical crimping of conductors with increased insulation

### Key commercial data

Packing unit	1000 pc
Minimum order quantity	1000 pc
GTIN	 4 017918 190125
Weight per Piece (excluding packing)	0.11 g
Custom tariff number	85369010
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	14 mm
Sleeve length	8 mm
Inner dimension of the insulating collar (d)	3.7 mm
Ferrule diameter	1.8 mm
Insulating collar thickness	0.3 mm
Sleeve wall thickness	0.15 mm

#### Ambient conditions

Short-term temperature	120 °C
Max. permanent temperature	105 °C

#### General

Color	black
Components	free from silicone and halogen
Inflammability class according to UL 94	HB

# Ferrule - AI 1,5 - 8 BK-GB-1000 - 3202892

## Technical data

### General

Material	E-CU
----------	------

### Classifications

#### eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201
eCl@ss 8.0	27400201

#### ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005

#### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

## Approvals

### Approvals

---

#### Approvals

CSA / CSAus / cCSAus

---

#### Ex Approvals

---

#### Approvals submitted

---

#### Approval details

## Ferrule - Al 1,5 - 8 BK-GB-1000 - 3202892

### Approvals

CSA 

CSAus

cCSAus