

## secvest.®

FU8002

## Secvest 2WAY Complete Package (DE, NL, FR)

The Secvest 2WAY is the high-end wireless alarm center from ABUS Security-Center, setting new design and function standards with a maximum range of functions, bidirectional wireless control elements and innovative backlight function.

The complete package provides all important components for effective protection and can be extended at any time, if required. For installation, 48 zones for wireless detectors and two lines for wired detectors are available. Communication between the center and the individual components works on 868.6625 MHz, a radio frequency that is reserved exclusively for security purposes. Up-to-date frequency-modulated wireless technology with millions of codes and duplex antenna technology guarantee reliable transmission of signals and quick and easy installation of the system and its components. Depending on structural conditions, the wireless coverage is approx. 30 meters indoors and up to 100 meters outdoors.

The system can easily be expanded at any time with additional or new components (wireless glass breakage detector, wireless seismic sensor, wireless emergency call transmitter, etc.). You can choose between German, Dutch and French for operating and programming.

You can find more information about the Secvest 2WAY and the included components in the individual data sheets.



### Product highlights:

- Ideal basic equipment for protection against intrusion and fire
- Freely extensible for apartment, home, and office building
- 2 motion detectors for indoor surveillance
- Magnetic contact for monitoring window or door
- Optical wireless smoke detector with maximum temperature sensor
- Bidirectional wireless remote control with status LED
- Proximity chip key
- 
- 
-

secvest.®

FU8002

## Secvest 2WAY Complete Package (DE, NL, FR)

### Technical Data

[Redacted]

[Redacted]

[Redacted]