



	F (N)	EL (mm)			ESD	No.
A EcoFlow roller – plastic	150	105 ... 605				3 842 994 989/L
		225				3 842 525 740
		325				3 842 525 741
		425				3 842 525 742
		525				3 842 537 164
B EcoFlow roller – steel, galvanized	500	105 ... 1005				3 842 994 988/L
		225				3 842 525 737
		325				3 842 525 738
		425				3 842 525 739
		525				3 842 537 163
C EcoFlow roller – stainless steel	150	105 ... 1005				3 842 995 008/L
D EcoFlow roller carrier				10		3 842 535 683
E EcoFlow section profile		30 ... 6070	1			3 842 993 029/L
		6070	20			3 842 537 321
F MV45 guide profile		30 ... 3000	1			3 842 993 511/L
		3000	10			3 842 525 443
		30 ... 3000	1			3 842 993 512/L
		3000	10			3 842 526 034
G Rail holder with stop				20		3 842 537 664
H Rail holder without stop				20		3 842 537 665
I Stop plate with stop				20		3 842 537 593
J Stop plate without stop				20		3 842 537 592