

DOOR-COUPLING ROTARY MECHANISM IP64,
EMERGENCY STOP, SIZE S00...S3, 330 MM SHAFT



General technical data:

product brand name		SIRIUS
Product designation		door-coupling rotary operating mechanism
Size of the circuit-breaker		S00, S0, S2, S3
Design of the product		EMERGENCY OFF door-coupling rotary operating mechanism
Control version of the switch operating mechanism		long shaft
Suitability for use		Circuit breaker S00, S0, S2, S3
Protection class IP on the front		IP64
Ambient temperature		
• during storage	°C	-50 ... +80
• during operation	°C	-20 ... +70
Operating frequency maximum	1/h	15
Color of the actuating element		red / yellow

Installation/ mounting/ dimensions:

Mounting position		any
Mounting type		screw fixing
Width	mm	66
Height	mm	66

Depth	mm	50
Length	mm	330
Diameter	mm	22.5
Required spacing for grounded parts		
• forwards	mm	0
• Backwards	mm	0
• upwards	mm	0
• at the side	mm	0
• downwards	mm	0

Certificates/ approvals:

Certificate of suitability

CE / UL / CSA

General Product Approval	Declaration of Conformity	Shipping Approval	other
--------------------------	---------------------------	-------------------	-------



[Bestätigungen](#)

[Umweltbestätigung](#)



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV29260L>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/ww/en/ps/3RV29260L>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV29260L&lang=en



last modified:



07.12.2015