

Datasheet

RS Pro On/Off Temperature Controller, 77 x 35mm, J Type Thermocouple Input, 230 V ac Supply

RS Stock No: 786-4766



Product Details

RS Pro on/off temperature controller measuring 77 x 35 mm works with type J thermocouple input using 230 V ac supply. These heating & refrigeration controllers are designed for measuring and controlling temperature. They can be used in many applications with their easy use, on/off control.

Features and Benefits

- 3 & 4 digits display options available
- On/Off temperature control
- Adjustable temperature offset
- Set value low limit and set value high limit boundaries
- Relay and SSR driver outputs available
- Single & dual set temperature controllers available
- Digital Input (cooking time start/stop input)
- Temperature control with manual heating function
- Alarm parameters

Specifications:

Input Type	J Type Thermocouple
IP Rating	NEMA 4X
Maximum Operating Temperature	+50°C
Minimum Operating Temperature	0°C
Mounting Type	DIN Rail
Number of Inputs	1
Number of Outputs	1
Output Type	Relay
Panel Depth	58.5 mm
Size	77 x 35 mm
Supply Voltage	230 V ac
Termination Type	Screw
Panel Cut Out Size	71 x 29 mm