


Cable tie - WT-STEEL SH 7,9X838 - 3240766

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable binders, made from rust-free stainless steel (AISI 316), suitable for the harshest of ambient conditions (for example, salt water), with ball lock, for quick and secure bundling and fastening

Key commercial data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 704847
Weight per Piece (excluding packing)	99.99 g
Custom tariff number	73269098
Country of origin	United Kingdom

Technical data

Dimensions

Length (b)	360 mm
Width (a)	4.8 mm
Max. material thickness	0.25 mm

Ambient conditions

Ambient temperature (operation)	-80 °C ... 538 °C
---------------------------------	-------------------

General

Color	silver
Type	Steel strip
Components	free from silicone and halogen
Material	Stainless steel 1.4401/AISI 316

Classifications

eCl@ss

eCl@ss 4.0	27140702
eCl@ss 4.1	27140702
eCl@ss 5.0	27140702

Cable tie - WT-STEEL SH 7,9X838 - 3240766

Classifications

eCl@ss

eCl@ss 5.1	27140702
eCl@ss 6.0	27140702
eCl@ss 7.0	27140702
eCl@ss 8.0	27140702

ETIM

ETIM 3.0	EC000046
ETIM 4.0	EC000046
ETIM 5.0	EC000046

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

Approvals

Approvals

Approvals

LR

Ex Approvals

Approvals submitted

Approval details

LR

Accessories

Accessories

Universal tools

Cable tie - WT-STEEL SH 7,9X838 - 3240766

Accessories

Cable tie tool - UNIFOX-CT M 7,9 - 1212610



Cable binder pliers, for steel cable binders with a width of up to 7.9 mm, for a material thickness of up to 0.3 mm

Phoenix Contact 2014 © - all rights reserved
<http://www.phoenixcontact.com>