




POL	MATERIAL NO.	ENGINEERING NO.
4	1200850011	WA4000-31
5	1200850012	WA5000-31

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	PA	BLACK
2	HOUSING	PA	BLACK
3	CONTACT	BRASS / GOLD	CuZn Ni/ Au
4	PG NUT	PA	BLACK
5	O-RING	VITON	RED
6	GROMMET	CR	BLACK
7	ULTRA-LOCK	BRASS /ST.STEEL	NICKEL PLATED

VOLTAGE RATING: 250 VAC/VDC
AMPERAGE RATING: 4A
PROTECTION CLASS: IP 67/68/69K
OPERATING TEMPERATURE: -25°C / 90°C
UL CERTIFICATION: FILE NO. E152210
CSA CERTIFICATIONS: FILE NO. LR6837

ENTER DESCRIPTION EC NO: WEU2010-0320 DRWN:STAUDIGEL 2010/02/02 CHKD: 2010/02/05 APPR:FPACHER 2010/02/05 REV 1	DESCRIPTION	QUALITY SYMBOLS ▽=0 ◇=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	TITLE M12U FA FEM STR PG7		
				mm	INCH	DRAWN BY NSTAUDIGEL	DATE 2010/02/02	DOCUMENT NO. SD-120085-004			SHEET NO. 1 OF 1	
			4 PLACES	± ---	± ---	CHECKED BY	DATE	MOLEX INCORPORATED			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
			3 PLACES	± ---	± ---							
			2 PLACES	± 0.05	± ---							
1 PLACE	± 0.1	± ---	APPROVED BY FPACHER		DATE 2010/02/05							
			ANGULAR ± ---°		MATERIAL NO.							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3							