

CHERRY B.UNLIMITED AES



Models may vary from the image shown

Secure data transmission and an advanced power supply.

The wireless desktop set CHERRY B.UNLIMITED AES combines guaranteed secure data transmission and an advanced energy supply, in a design which has been thought through to the very last detail. For high professional requirements and security both at home and in the workplace.

Key benefits

- Data transmission using 128-bit encryption, complying to Advanced Encryption Standard (AES)
- USB cable charging function for both keyboard & mouse – even when in use
- High-quality, pre-charged NiMH batteries from GP with a very low self-discharge
- Interference-free, wireless 2.4 GHz technology – with a range of approx. 10 m
- 3-button mouse: infrared sensor and adjustable resolution (1,000/2,000 dpi) with ergonomic side panels
- Easy to install, requiring no technical knowledge
- Mini USB receiver

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

Product dependant, see table "Models"

Key colour:

Product dependant, see table "Models"

Weight (product):

approx. 883 g (keyboard with batteries), approx. 145 g (mouse with batteries), approx. 6 g (receiver)

Total weight (with packaging):

approx. 1304 g

Transmission range:

approx. 10 m

Frequency range:

2.400 GHz - 2.4835 GHz

Storage Temperature:

-20°C to 65°C

Operating Temperature:

0°C to 40°C

Current Consumption:

typ. 3 mA (keyboard), typ. 10 mA (mouse), typ. 30 mA (receiver)

Interface:

- USB

Connection sockets:

- Low voltage socket for USB charging cable

Product approvals:

- c-tick 
- UL 
- CE 
- FCC 
- TÜV/GS 

System requirements:

- USB port for wireless receiver (second free USB port for using the charger cable during operation)

Delivery Volume:

- 1 signal receiver
- USB charger cable
- Operating instructions in hard copy
- 1 optical wireless mouse
- 1 wireless keyboard
- 2 LSD NiMH batteries (type AAA)
- 2 LSD NiMH batteries (type AA)

Dimensions (product):

approx. 460 x 165 x 15 mm (keyboard), approx. 115 x 60 x 35 mm (mouse), approx. 42 x 18 x 8 mm (receiver)

Packaging dimensions:

approx. 570 x 170 x 45 mm

Mouse:

- Scanning: Infrared
- Resolution: 1000 / 2000 dpi (adjustable)
- Number of Keys: 3
- Mouse wheel design: Scroll wheel with key function
- Design: Symmetrical
- Connection: wireless
- Housing colour: Product dependant, see table "Models"
- Key colour: Product dependant, see table "Models"

Keyboard:

- Key technology: SX
- Service life, standard key: > 10 million key operations
- Inscription layout: Standard
- Number of Keys: Product dependant, see table "Models"

Packaging Unit:

- Number of products in the master package: 6
- Number of master packages per pallet: 24

Warranty:

2 years

Errors, technical changes and delivery possibilities excepted.
Technical information refers only to the specifications of the
products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Number of Keys	Mouse Housing colour	Mouse Key colour
1	CHERRY B.UNLIMITED AES	JD-0400BE-0-	4025112079955	Belgium	light grey	light grey	105+4	light grey	light grey
2	CHERRY B.UNLIMITED AES	JD-0400BE-2-	4025112079887	Belgium	black	black	105+4	black	black
3	CHERRY B.UNLIMITED AES	JD-0400CH-0-	4025112079962	Switzerland	light grey	light grey	105+4	light grey	light grey
4	CHERRY B.UNLIMITED AES	JD-0400CH-2-	4025112079894	Switzerland	black	black	105+4	black	black
5	CHERRY B.UNLIMITED AES	JD-0400DE-0	4025112078927	Germany	light grey	light grey	105+4	light grey	light grey
6	CHERRY B.UNLIMITED AES	JD-0400DE-2	4025112078941	Germany	black	black	105+4	black	black
7	CHERRY B.UNLIMITED AES	JD-0400ES-0-	4025112079993	Spain	light grey	light grey	105+4	light grey	light grey
8	CHERRY B.UNLIMITED AES	JD-0400ES-2-	4025112079948	Spain	black	black	105+4	black	black
9	CHERRY B.UNLIMITED AES	JD-0400EU-0	4025112078934	US English with EURO symbol	light grey	light grey	104+4	light grey	light grey
10	CHERRY B.UNLIMITED AES	JD-0400EU-2	4025112078958	US English with EURO symbol	black	black	104+4	black	black
11	CHERRY B.UNLIMITED AES	JD-0400FR-0-	4025112079979	France	light grey	light grey	105+4	light grey	light grey
12	CHERRY B.UNLIMITED AES	JD-0400FR-2-	4025112079924	France	black	black	105+4	black	black
13	CHERRY B.UNLIMITED AES	JD-0400GB-0-	4025112080005	UK	light grey	light grey	105+4	light grey	light grey
14	CHERRY B.UNLIMITED AES	JD-0400GB-2-	4025112079788	UK	black	black	105+4	black	black
15	CHERRY B.UNLIMITED AES	JD-0400IT-0-	4025112079986	Italy	light grey	light grey	105+4	light grey	light grey
16	CHERRY B.UNLIMITED AES	JD-0400IT-2-	4025112079931	Italy	black	black	105+4	black	black
17	CHERRY B.UNLIMITED AES	JD-0400PN-0-	4025112080630	Pan-Nordic	light grey	light grey	105+4	light grey	light grey
18	CHERRY B.UNLIMITED AES	JD-0400PN-2-	4025112080647	Pan-Nordic	black	black	105+4	black	black