



ENGLISH

Datasheet

Stock No: 534-755

RS Pro 38 Series Blue Insulated Crimp Receptacle, 4.8 x 0.5mm, 16 → 14 AWG, Tin Plated



Product Details

RS Shrouded Receptacles

A range of fully insulated shrouded female disconnect crimp receptacles with a copper sleeve and a choice of insulation types as follows:

Part numbers ending in 'VH' have a flared vinyl insulation

Part numbers ending in 'FEH' have funnel entry polycarbonate insulation

These insulated shrouded female disconnect crimp receptacles are available with a various wire ranges and tab sizes.

Red 0.5 - 1.5 mm²

Blue 1.5 - 2.5 mm²

Yellow 2.5 - 6.5 mm²

RS Pro Range

Conversion table	
M3 / 6 BA	M5/ 2BA
M3.5/ 4BA	M6/ 0BA
M4/ 3BA	

Wire Sizes	
Mini Yellow	0.2 - 0.5 mm ²
Red	0.5 - 1.5 mm ²
Blue	1.5 - 2.5 mm ²
Yellow	2.5 - 6.5 mm ²

Technical Specification	
Temperature rating	+70°C
Body Material	Copper
Body Plating	Tin



ENGLISH

Specifications:

Tab Size	4.8 x 0.5mm
Colour	Blue
Insulation	Insulated
Wire Size	16 → 14 AWG
Gender	Female
Connector Type	Tab
Series	38
Contact Material	Brass
Contact Plating	Tin
Length	20.2mm
Insulation Material	Vinyl