



ENGLISH

Datasheet

**RS Pro Galvanised Steel Adjustable Height Mount 120mm  
Rubber 59mm 1000kg 120mm M16 0°**

RS Stock No: **688-212**



## Product Details

RS Pro galvanised steel adjustable height mount is suitable for precision installation of machine tools, printing presses and other industrial machines. The levelling plate of this anti-vibration mount can be height adjusted to suit your installation needs. Ideal for absorbing vibration and reducing noise. The RS mount is also durable to industrial environments because of the galvanised steel and oil resistant rubber base.

## Features and Benefits

- Precision installation of machine tools, printing presses and other industrial machines
- Absorbs vibration and reduces noise levels
- Galvanised steel with oil resistant rubber base
- Accurate height adjustment with fine pitch screw
- Highly resistant to horizontal forces
- 1000 kg static load capacity
- Rubber foot



**Specifications:**

Base Material	Galvanised Steel
Diameter	120 mm
Foot Material	Rubber
Overall Height	59 mm
Static Load Capacity	1000 kg
Thread Length	120 mm
Thread Size	M16
Tilt Angle	0°