



AMP WIRE RANGE	 E13288 Listed
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED

 LR7189 Certified	MILITARY P/N AND CLASS
12-10 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1


STAMP AMP 12-10* APPROX AS SHOWN
- 2

0.00254 [.000100] MIN TIN PER
ASTM B-545
- 3

CLEANED, UNPLATED

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm²[5,180-13,100] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

3	-	LOOSE PIECE	322455-1
2	2500	ON TAPE	2-322455-1
2	----	LOOSE PIECE	322455
FINISH	QUANTITY	PACKAGING TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-17-93	 TE Connectivity			
DIMENSIONS: INCHES		CHK DA PATTERSON 3-17-93				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD DE MILLER 3-17-93			
	FINISH SEE TABLE		PRODUCT SPEC			
MATERIAL COPPER PER ASTM B-152 ANNEALED		APPLICATION SPEC	WEIGHT		SIZE A2	
			CAGE CODE 00779		DRAWING NO C-322455	
		CUSTOMER DRAWING	SCALE 10:1		SHEET 1 of 1	
			RESTRICTED TO		REV E1	