



Price* : 12.06 GBP



Main

Range	Lineryg
Product name	HK
Product or component type	Plug outlet
Poles description	3P + N
[I _{th}] conventional free air thermal current	32 A
I ² t on activation	200000 A ² .s
Number of points	2
Number of cables	4 cable(s) 4 mm ²
Cable length	0.25 m
Quantity per set	Set of 6

Complementary

[Ui] rated insulation voltage	600 V conforming to UL 690 V conforming to IEC 60439-1 600 V conforming to CSA
Peak current	25 kA
Width	18 mm
Height	45.5 mm
Depth	38 mm
Product weight	0.05 kg

Environment

Standards	IEC 60439
Product certifications	CSA DNV LROS (Lloyds register of shipping) UL

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0713 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------