

**FEATURES**

- One of the lightest gloves in the industry for maximum comfort
- Patented FT™ nitrile foam coating enhances protection as well as providing good wet grip by channeling away excess fluid from the glove surface
- Excellent resistance to abrasion
- Flexible and comfortable, with excellent dexterity

**DESCRIPTION**

- Machine knitted liner made from Nylon/Spandex which gives good fit and sensitivity, superior comfort and dexterity
- 18gg seamless liner glove with solid knit wrist
- Patented NFT™ nitrile foam coating for better grip in wet, oily or dry conditions
- Treated with Actifresh to kill bacteria and promote freshness
- Red colouring



**TECHNICAL DATA**

**AVAILABLE SIZES** 7/S • 8/M • 9/L • 10/XL

**PACKAGING** 10/120  
*Pairs per pack/box*

**COLOUR OF LINER/COATING** Red/Black

**TYPICAL APPLICATIONS**

- Automotive
- Quality Inspection
- Goods handling
- Assembly and Maintenance
- Light fabrication
- Handling mild abrasive surfaces

**Cat**  
CE II



**EN 388 standard**

Abrasion 4  
Cut 1  
Tear 2  
Puncture 1

EN388: 2003



**Recommendations For Use**

- Do not use near moving machines if there is a risk of entanglement.
- Storage: Gloves should be ideally stored in cool, dry conditions in original packaging and away from direct sunlight.
- Cleaning/Maintenance: Both new and used gloves should be thoroughly inspected before being worn to ensure no damage is present. Gloves should not be left in contaminated condition if reuse is intended in which case gloves should be cleaned as far as possible. If appropriate, decontamination may take place under lukewarm water using laundry soap and detergent. Don't use chlorine bleaches.