Sockets



Product description

Sockets are built in equipment, housings or panels and permit the rapid, simple connection of measuring leads, plugs or, when configured as pole terminals, the secondary connection of leads and cable lugs.
Tin plated and gold plated surfaces, and a choice of connector cross sections, permit the reliable transmission of low-level signals and powerful currents.
The insulation of the PKI 110 incorporates a spring which permits leads to be efficiently connected in the minimum of time.

*System Article type		Technical Data	**Order no. Colour**
②		6 A	**930 312-000**
MBU 1			
②		6 A	**931 337-000**
MBU 2			
④		16 A opening for installation ø 6 mm	**930 160-000**
BO 10			
④		16 A opening for installation ø 6 mm	**930 147-000**
BU 10			

*System Article type		Technical Data	**Order no. Colour**
④		16 A opening for installation ø 6 mm	**930 177-000**
BU 20			
②		6 A	**930 224-100** ● **930 224-101** ●
MPB 1			
④		16 A	**973 582-100** ● **973 582-101** ●
PB 4			
②		6 A	**930 308-100** ● **930 308-101** ● **930 308-102** ● **930 308-103** **930 308-104** **930 308-106**
MBI 1			

* System: (64) = 0.64 mm system / ② ≙ 2 mm system / ④ ≙ 4 mm system / ⦿ ≙ 4 mm safety system / ↔ ≙ 4 mm sliding sleeve system

HIRSCHMANN

*System Article type		Technical Data	Order no. Colour
④  BIL 20		max. 32 A opening for installation ø 8 mm	**930 176-100** ● **930 176-101** ● **930 176-102** ● **930 176-103** **930 176-104** ● **930 176-107**
④ BIL 30		max. 32 A opening for installation ø 8 mm	**930 166-100** ● **930 166-101** ●
④ BUG 10		max. 32 A opening for installation ø 6 mm	**930 175-100** ● **930 175-101** ● **930 175-102** ● **930 175-103** **930 175-104** ● ○
⦿ SEB 2600 G M4		32 A screw connection, M4, solder	**972 354-100** ● **972 354-101** ● **972 354-102** ● **972 354-103** **972 354-104** ● **972 354-188**
⦿ SEB 2610 F4,8		24 A 4.8 x 0.8, tab connector	**972 355-100** ● **972 355-101** ● **972 355-102** ● **972 355-103** **972 355-104** ● **972 355-188**

*System Article type		Technical Data	Order no. Colour
⦿ SEP 2610-F4,8		24 A press-fit sleeve, tab connector 4.8 x 0.8	**972 361-100** ● **972 361-101** ● **972 361-102** ● **972 361-103** **972 361-104** ● **972 361-188**
⦿ SEB 2620 F6,3		32 A 6.3 x 0.8, tab connector	**972 356-100** ● **972 356-101** ● **972 356-102** ● **972 356-103** **972 356-104** ● **972 356-188**

* System: ⑥④ = 0.64 mm system / ② ≙ 2 mm system / ④ ≙ 4 mm system / ⦿ ≙ 4 mm safety system / ⇹ ≙ 4 mm sliding sleeve system

HIRSCHMANN

Sockets

*System Article type		Technical Data	Order no. Colour
⊙ SEP 2620-F6,3		32 A press-in socket, tab connector 6.3 x 0.8	**972 362-100** ● **972 362-101** ● **972 362-102** ● **972 362-103** **972 362-104** ● **972 362-188** ●
⊙ SEB 2630-S1,9		24 A soldering spike 1.9 mm	**972 359-100** ● **972 359-101** ● **972 359-102** ● **972 359-103** **972 359-104** ● **972 359-188** ●
⊙ SEP 2630-S1,9		24 A press-in socket, soldering spike 1.9 mm	**972 363-100** ● **972 363-101** ● **972 363-102** ● **972 363-103** **972 363-104** ● **972 363-188** ●
② MPK 1		6 A	**930 268-100** ● **930 268-101** ●
④ PK 10 A		max. 35 A opening for installation ø 6 mm	**930 099-100** ● **930 099-101** ● **930 099-102** ● **930 099-103** **930 099-104** ● **930 099-188** ●

*System Article type		Technical Data	Order no. Colour
④ PKI 10 A		max. 35 A	**930 103-100** ● **930 103-101** ● **930 103-102** ● **930 103-103** **930 103-104** ● **930 103-188** ●
④ PKN 10 B		63 A	**930 117-100** ● **930 117-101** ●
④ PKNI 10 B		63 A	**930 136-100** ● **930 136-101** ●
④ PKNI 20 B		63 A	**930 144-100** ● **930 144-101** ●
④ PK 110		max. 35 A opening for installation ø 6 mm	**931 713-100** ● **931 713-101** ●

* System: (64) = 0.64 mm system / ② ≙ 2 mm system / ④ ≙ 4 mm system / ⊙ ≙ 4 mm safety system / ↔ ≙ 4 mm sliding sleeve system

HIRSCHMANN

*System Article type		Technical Data	**Order no. Colour**	Notes
④ PKI 110		max. 35 A	**931 714-100** ● **931 714-101** ● **931 714-102** ● **931 714-103** **931 714-104** ● **931 714-188** ◐	
④ PKI 100		max. 35 A	**930 757-100** ● **930 757-101** ● **930 757-102** ● **930 757-103** **930 757-104** ● **930 757-188** ◐	
⦿ SAB 2600 G M4		32 A surface-mounted socket, screw connection, M4	**972 357-100** ● **972 357-101** ● **972 357-102** ● **972 357-103** **972 357-104** ● **972 357-188** ◐	

* System: ⑥④ = 0.64 mm system / ② ≙ 2 mm system / ④ ≙ 4 mm system / ⦿ ≙ 4 mm safety system / ↔ ≙ 4 mm sliding sleeve system

HIRSCHMANN