

Datasheet

Art.No. R1.190.1110.0

Configurable control component SP-COP1-A DC 24V

samosPRO-Compact module, 20 safe inputs, 4 safe outputs, USB-Interface, Pluggable screw-terminals



Art.No.	R1.190.1110.0
EAN	4049088257742
Order unit	1 pieces

Approvals



Technical data

**Connection Data**

Type of electric connection	Screw connection
Detachable clamps	Yes

**Output circuit**

Number of outputs	8
Output current	4 A
Short-circuit protection, outputs	Yes
Type of digital output	Transistor
Min. allowed output voltage	16.2 V
Max. allowed output voltage	30 V
Number of digital outputs, integrated	8

**Control circuit**

Min. rated DC voltage for controls	15.6 V
Max. rated DC voltage for controls	30 V
Input current with signal 1	2.3 mA
Permitted voltage at input	30 V

**Supply circuit**

Min. supply voltage	16.8 V
Max. supply voltage	30 V

**Dimensions**

Depth	115 mm
Width	45 mm
Height	96 mm

**Classification**

ETIM 5.0	EC002538: Configurable control component
ETIM 4.0	EC002538: Configurable control component

Drawings

