




DO NOT SCALE


DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION



5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



DOC. CENTRE
14 JUNI 1993

NOTES: 1 FOR USE ON STANDARD AND MINIATURE APPLICATORS

2 FOR USE ON MINIATURE APPLICATORS. (AMP-O-MATOR APPLICATION)

3 WITH PAPER COVER 4 WITH PAPER LAYER

NOTES	FINISH	MATERIAL	PART NUMBER
5 OBSOLETE	UNPLATED	PHOSPHOR BRONZE	160134-7
	TIN PLATED	PHOSPHOR BRONZE	160134-6
	UNPLATED	PHOSPHOR BRONZE	160134-5
5 OBSOLETE	UNPLATED	BRASS	160134-4
	UNPLATED	PHOSPHOR BRONZE	160134-3
	TIN PLATED	BRASS	160134-2
	UNPLATED	BRASS	160134-1

CUSTOMER DRAWING

FOR REFERENCE ONLY
WILL NOT BE UPDATED

AMP

AMP-HOLLAND B.V.
's-Hertogenbosch, The Netherlands

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

19

© COPYRIGHT 19 BY AMP-HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED.
AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

DR. 21/6.83	WIRE RANGE 3.1 - 3.3 mm	NAME RING TONGUE WITH INSULATION SUPPORT	REV. DATE D M Y
CHK. 21/6.83	INSUL. RANGE 3.0 - 5.3 DIA.		26 11 09
APP. 28.4.83	SIZE A4	SHEET 1 OF 1	REV. LTR. B1

DRAWING NO
C-160134