

General Information

Extended Product Type:	OHBS12
Product ID:	1SCA108252R1001
EAN:	6417019416151
Catalog Description:	Handle OHBS12
Long Description:	For shaft diameter 6 mm, door drilling 22.5 mm. Indication I-O and ON-OFF. IP65 handles, NEMA 1, 3R, 10

Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

Ordering

EAN:	6417019416151
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85389099

Dimensions

Product Net Width:	20 mm
Product Net Height:	20 mm
Product Net Depth:	20 mm
Product Net Weight:	0.018 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	20 mm
Package Level 1 Height:	20 mm
Package Level 1 Length:	20 mm
Package Level 1 Gross Weight:	0.018 kg
Package Level 1 EAN:	6417019416151

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
--------------	---

Additional Information

Handle Type:	Knob
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	10 piece
Product Main Type:	OHBS12
Product Name:	HANDLE
Suitable For:	OT16-40
Suitable for Product Class:	Switch disconnectors

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
Declaration of Conformity - CE:	1SCC390030D0203

Classifications

ETIM 5.0:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

