

# ISDN STAR 1/4

Montageanweisung / Assembly Instruction



Telegärtner

<p>①</p>	<p>② Option A: Steckanschluss Patch solution</p> <p>NTBA</p>	<p>③</p> <p>Zulässige gesamt Kabellänge / max. 300 m Cat.3 Kabel/cable total allowable cable length: max. 400 m Cat.5 Kabel/cable</p>																		
<p>Lieferumfang/Scope of delivery J02020A0014 RAL 7035</p>																				
<p>④ Option B: Festverdrahtung fixed wiring</p>	<p>⑤</p> <p>123 mm</p>	<p>⑥</p>																		
<p>⑦</p>	<p>⑧</p> <p>NTBA</p>	<p>⑨</p>																		
<p>⑩</p>	<p>⑪</p>	<table border="1"> <tr> <td>4</td> <td>a1</td> <td>1a</td> <td>rt</td> <td rowspan="2">} Paar / Pair 1</td> </tr> <tr> <td>5</td> <td>b1</td> <td>1b</td> <td>sw</td> </tr> <tr> <td>3</td> <td>a2</td> <td>2a</td> <td>ws</td> <td rowspan="2">} Paar / Pair 2</td> </tr> <tr> <td>6</td> <td>b2</td> <td>2b</td> <td>ge</td> </tr> </table> <p>Drahtfarben bei Kabel J-Y (ST) Y2x2x0,6Lg Wire colours for cable</p> <p>Klemmbezeichnung Terminal designation</p> <p>S<sub>0</sub>-Bezeichnung der Leitung S<sub>0</sub>-designation of wires</p> <p>Kontakt-Nr. RJ45-Buchse Contact N<sub>j</sub> RJ45 jack</p>	4	a1	1a	rt	} Paar / Pair 1	5	b1	1b	sw	3	a2	2a	ws	} Paar / Pair 2	6	b2	2b	ge
4	a1	1a	rt	} Paar / Pair 1																
5	b1	1b	sw																	
3	a2	2a	ws	} Paar / Pair 2																
6	b2	2b	ge																	