

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 70107-0046
Status: Active
Overview: SL™ Modular Connectors
Description: SL™ Wire-to-Wire Panel Mount Crimp Housing, Single Row, Version B, with Mounting Ears, 12 Circuits

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)

[Product Specification PS-70400 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series 70107
Application Signal, Wire-to-Wire
Overview SL™ Modular Connectors
Product Name SL™
UPC 800754347273

Physical

Circuits (maximum) 12
Color - Resin Black
Flammability 94V-0
Gender Male
Glow-Wire Compliant No
Material - Resin Polyester
Net Weight 2.685/g
Number of Rows 1
Packaging Type Bag
Panel Mount Yes
Pitch - Mating Interface 2.54mm
Temperature Range - Operating -40°C to +120°C

Material Info

Reference - Drawing Numbers

Product Specification PS-70400
Sales Drawing SD-70107-0036-0059



Series

image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
70107Series

Mates With
70066 SL™ Crimp Housing A, G and D
(Notes: Version C and H will not mate to the 70107 housing series), 70400 SL™ Insulation Displacement Connector Assembly, Version G Housing, 70430 SL™ Single Row Receptacle, Version G

Use With
70021