

Professionally approved products.

Datasheet

Steel Clear Passivated, Galvanised ¼ Turn Fasteners for 19 in. Racking

RS Stock number [278-461](#)



Description:

Two sizes of slotted-head 'Panex' fasteners which offer quick access to equipment, but safe, positive locking of the access panel in the closed position. The stud is retained by means of a plastic washer (supplied).

Zinc plated & chromate passivated steel construction.

Choice of two sizes suits most commonly used panel thicknesses.

No specialised tools required for fixing.

Specifications:

Material:	Steel
Finish:	Clear Passivated, Galvanised
Head Type:	Rounded
Drive Type:	Phillips
For Panel Thickness (Maximum):	4.4 mm
For Panel Thickness (Minimum):	3.5 mm