

Circuit breakers for power distribution

A1 Ordering information



A1 100A - Fixed (F) 1 pole - Front terminals (F)
Thermomagnetic trip unit - TMF Icu (240 V)

In	I ₃	A (10kA)	N (18kA)
15	400	A1A015TW-1	A1N015TW-1
20	400	A1A020TW-1	A1N020TW-1
25	400	A1A025TW-1	A1N025TW-1
30	400	A1A030TW-1	A1N030TW-1
40	400	A1A040TW-1	A1N040TW-1
50	500	A1A050TW-1	A1N050TW-1
60	600	A1A060TW-1	A1N060TW-1
70	700	A1A070TW-1	A1N070TW-1
80	800	A1A080TW-1	A1N080TW-1
90	900	A1A090TW-1	A1N090TW-1
100	1000	A1A100TW-1	A1N100TW-1



A1 100A - Fixed (F) 2 pole - Front terminals (F)
Thermomagnetic trip unit - TMF Icu (240 V)

In	I ₃	A (10kA)	N (25kA)
15	400	A1A015TW-2	A1N015TW-2
20	400	A1A020TW-2	A1N020TW-2
25	400	A1A025TW-2	A1N025TW-2
30	400	A1A030TW-2	A1N030TW-2
40	400	A1A040TW-2	A1N040TW-2
50	500	A1A050TW-2	A1N050TW-2
60	600	A1A060TW-2	A1N060TW-2
70	700	A1A070TW-2	A1N070TW-2
80	800	A1A080TW-2	A1N080TW-2
90	900	A1A090TW-2	A1N090TW-2
100	1000	A1A100TW-2	A1N100TW-2



A1 100A - Fixed (F) 3 pole - Front terminals (F)
Thermomagnetic trip unit - TMF Icu (240 V)

In	I ₃	A (10kA)	N (25kA)
15	300	A1A015TW	A1N015TW
20	300	A1A020TW	A1N020TW
25	300	A1A025TW	A1N025TW
30	300	A1A030TW	A1N030TW
40	400	A1A040TW	A1N040TW
50	500	A1A050TW	A1N050TW
60	600	A1A060TW	A1N060TW
70	700	A1A070TW	A1N070TW
80	800	A1A080TW	A1N080TW
90	900	A1A090TW	A1N090TW
100	1000	A1A100TW	A1N100TW