




4	8630-CH37UNCLF	UNC 440
3	8630-CH37LF	M3
2	8630-CH37 UNC	UNC 440
1	8630-CH37	M3
SL.NO.	PART NO:	THREAD

CABLE ENTRY $\phi 14.0$ MAX.

THREAD

"This LF product meets European Union Directives and other country regulations as described in GS-22-008"

Packaging as per GS-14-920

MATERIAL:-

- 1.NYLON 6 30% GF UL 94V-0 (OPTIONAL)
- 2.ABS UNFILLED UL 94 HB (STANDARD)
- 3.TEMP RANGE -55°C +85°C

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM 	title CONNECTOR HOOD 37 POS			
D	106-0074	MINI	2006/06/08	angles	linear					
E	110-0122	AMR	2010/05/29	0°±1°						
F	110-0231	AMR	2010/11/27			scale —				
				dr	MINI K VANDANATH	1994/09/09			dwg no	sheet 1 of 1
				enr	ABHILASH M R	2010/05/29			C-DSUB-0025	size A4
				chr	ABHILASH M R	2010/05/29				
				app	SUDHIR VARMA	2010/05/29				
sheet index	revision	F								
	sheet	1								