



### Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch head
Device short name	ZC2J
Head type	Rotary head
Product compatibility	XC2J
Associated lever	ZC2JY11 ZC2JY12 ZC2JY13 ZC2JY31 ZC2JY51 ZC2JY81 ZC2JY91
Associated body	ZC2JC1 ZC2JC18 ZC2JC2 ZC2JC28 ZC2JD1 ZC2JD2
Movement of operating head	Rotary
Type of operator	Spring return without operating lever
Type of approach	1 direction lateral approach
Positive opening	Without

### Complementary

Switch actuation	CCW From right
Product weight	0.21 kg
Head material	Metal

### Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment