

# Specifications for BMP51/53 Labelmaker Labels

<b>Adhesive</b>	Permanent Acrylic
<b>Article No.</b>	143347
<b>Brady Material No.</b>	<a href="#">B-499</a>
<b>Material Type</b>	Nylon Cloth
<b>Colour</b>	Black on Yellow
<b>Finish</b>	Matt
<b>Order Reference</b>	M-83-499-YL-BK
<b>Printer Compatibility</b>	BMP41; BMP51; BMP53
<b>Size - Diameter</b>	12.70
<b>Additional Information</b>	Low profile; High adhesion
<b>Thickness (mm)</b>	0.166
<b>Total Qty per Pack</b>	240 Label(s) / Box
<b>Approval/Compliance</b>	UL Recognised; CSA Accepted; Halogen Free (DIN VDE 0472/part 815)
<b>Application</b>	Laboratory Identification
<b>Environment</b>	Freezer; Liquid Nitrogen; Autoclave
<b>Industry</b>	Healthcare; Laboratory
<b>Laboratory Application</b>	Centrifuge & PCR Tubes;Cryo Tubes
<b>Description</b>	Nylon cloth with permanent adhesive allows labelling in environments with heat, cold, oil and dirt. Ideal for wire and cable marking, electronic component marking, laboratory vial identification and general labelling. Please Note: This material is UL recognized with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.
<b>Max. Service Temp. °C</b>	90
<b>Min. Service Temp. °C</b>	-40
<b>Shape</b>	Circle
<b>Software</b>	LabelMark
<b>Surface</b>	For smooth, textured/rough or Highly textured/Low surface energy surfaces
<b>Vial/Tube (ml)</b>	1.5 - 2.0 ml