



-1. Wrenches

-1.1. OPEN END WRENCHES

- Single open end wrenches
- Standards: ISO 3318 and DIN 894
- Material: Standard alloy steel
- Open end angle 15°
- Gunmetal finishing

Single open end wrench

894M

				L mm	a mm	b mm	
894M-7	7314151833008	10	7	78	3.2	16	10
894M-8	7314151833015	10	8	94	3.5	18	14
894M-9	7314151833022	10	9	100	4.0	20	16
894M-10	7314151833039	10	10	106	4.5	22	20
894M-11	7314151833046	10	11	112	5.0	24	23
894M-12	7314151833053	10	12	125	5.0	26	30
894M-13	7314151833060	10	13	125	5.0	29	40
894M-14	7314151833077	10	14	140	5.5	30	40
894M-15	7314151833084	10	15	140	5.5	32	49
894M-16	7314150139569	10	16	140	5.5	32	49
894M-17	7314151833091	10	17	158	6.0	36	55
894M-19	7314151833107	10	19	171	7.0	40	75
894M-21	7314150223220	5	21	195	7.5	45	90
894M-22	7314151833114	5	22	195	8.0	46	100
894M-24	7314151833121	5	24	216	9.0	50	150
894M-27	7314151833138	5	27	240	10.0	56	215
894M-30	7314151833145	5	30	262	11.0	62	270
894M-32	7314151833152	5	32	274	12.0	67	320
894M-34	7314150139583	1	34	274	12.0	67	320
894M-36	7314151833169	5	36	303	13.0	74	400
894M-38	7314151833176	1	38	305	13.0	78	420
894M-41	7314151833183	1	41	343	14.0	85	590
894M-46	7314151833190	1	46	378	15.0	94	750
894M-50	7314151833206	1	50	413	16.0	102	945
894M-55	7314151833213	1	55	457	17.0	113	1185
894M-60	7314151833220	1	60	492	18.0	122	1380
894M-65	7314151833237	1	65	528	19.0	132	1750
894M-70	7314151833244	1	70	573	20.0	142	2270
894M-75	7314151833251	1	75	608	21.0	152	2770
894M-80	7314151833268	1	80	644	22.0	162	3180
894M-85	7314151833275	1	85	690	23.0	174	3630
894M-90	7314151833282	1	90	690	25.0	174	3630
894M-95	7314151833299	1	95	850	25.0	195	5750
894M-100	7314151833305	1	100	1000	28.0	195	5530
894M-105	7314151833312	1	105	1000	28.0	215	7300
894M-110	7314151833329	1	110	1000	28.0	215	7300
894M-115	7314151833336	1	115	1000	28.0	215	7300
894M-120	7314151833343	1	120	1000	28.0	215	7300
894M-125	7314150132478	1	125	1000	28	225	7300
894M-130	7314150132485	1	130	1000	28	225	7600
894M-135	7314150132492	1	135	1000	28	225	7400

