

Datasheet

RS Pro Non-Fused Terminal Block, 12 Way/Pole, Screw Terminals, 6 mm² Free Hanging, Panel Mount, PE, 380 V

RS Stock No: **763-8116**



Product Details

RS Pro non-fused terminal block comes with brass inserts and galvanised steel screws. This easy cut, low cost 12-way polyethylene terminal block operates at a voltage rating of 380 V and temperature rating of +80°C. It supports the wire size of 6 mm².

Features and Benefits

- All screws are captive and raised for easy wiring
- Comes in natural colour
- Temperature rating of +80°C



ENGLISH

Specifications:

Contact Material	Brass
Current Rating	5 to 32 A
Material	PE Housing
Maximum Operating Temperature	+80°C
Mounting Type	Free Hanging, Panel Mount
Number of Ways	12
Pitch	10 mm
Termination Method	Screw
Voltage Rating	380 V
Wire Size	6 mm ²
Colour	Natural
Dimensions	115 x 18.8 x 15 mm
Standards Met	RoHS, CE