



ENGLISH

Datasheet

RS Pro Swivel Plate Castor PR100ASF, 75kg

RS Stock No: **666-7567**



Product Details

RS Pro swivel castor has load capacity of 75 kg. A range of rubber tyred silent running castors come with a built-in synthetic thread guard.

Features and Benefits

- Silent running castors
- Precision ball bearing in wheel
- Reduces noise in the workplace
- Grey rubber tyre



ENGLISH

Specifications:

Features	Quiet Operation
Fixing Centres (Length)	80 mm
Fixing Centres (Width)	60 mm
Fixing Centres	80 x 60 mm
Fixing Hole Size	9 mm
Fixing Plate Dimensions	100 x 85 mm
Fixing Plate Length	100 mm
Fixing Plate Width	85 mm
Hub Bearing Type	Ball Bearing
Hub Material	PP
Includes Brake	Yes
Load Capacity	75 kg
Number of Fixing Holes	4
Overall Height	140 mm
Rotation	Swivel
Tyre Material	Rubber
Weight Class	Light Duty
Wheel Diameter	100 mm
Wheel Width	30 mm