

# Electronic housing - UM108-PROFIL 235CM BK - 2909963

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Drawn section panel mounting base, with a constructional width of 108 mm and a fixed length of 235 cm

The illustration shows the version UM 45-Profil CM, in green



## Key commercial data

Packing unit	1 CM
GTIN	 4 017918 419226
Weight per Piece (excluding packing)	1000.0 g
Custom tariff number	39162000
Country of origin	Germany

## Classifications

### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

### UNSPSC

UNSPSC 6.01	31261501
-------------	----------

# Electronic housing - UM108-PROFIL 235CM BK - 2909963

## Classifications

### UNSPSC

UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Accessories

### Accessories

#### Component housing cover

Electronic housing - UM-A/U N 73 CM - 2706852

U-shaped cover, flat-profile version, transparent, PC, high-temperature resistant material, please indicate length in [cm] with order no.

---

#### Component housing lower part

Electronic housing - UM108-LG 10 - 2959780

Profile housing and board base, 10 mm wide module, consisting of two side elements



---

#### Mounting material

Mounting flange - UMK-BF - 2976077

Mounting flange, for mounting directly on the wall



---

Electronic housing - UM108-FE - 2959463

Foot element, 107.5 mm wide, for mounting on NS 32 or NS 35/7.5, below profile housing UM 108.



## Electronic housing - UM108-PROFIL 235CM BK - 2909963

### Accessories

Mounting flange - UMK-BF - 2976077



Mounting flange, for mounting directly on the wall

---

### Panel mounting base side part

Electronic housing - UM108-SEPEF/L - 2906490



Side element, left, with foot, width: 5 mm, length: 108 mm, for mounting on NS 32 or NS 35/7.5, with PE contact to the DIN rail

---

Electronic housing - UM108-SE - 2959476



Side element, 5 mm wide, PCB width: 107.5 mm

---

Electronic housing - UM108-SEFE/R-A60 - 2959706



Side element, with foot, tall version, right-hand, for 60 mm wide U-shaped cover.

---

Electronic housing - UM108-SEFE/R-A73 - 2959719



Side element, with foot, tall version, right-hand, for 73 mm wide U-shaped cover.

## Electronic housing - UM108-PROFIL 235CM BK - 2909963

### Accessories

Electronic housing - UM108 N-SEFE/R-A73 - 2709354



Side element, with foot, low-profile version, right-hand, for 73 mm wide U-shaped cover.

---

Electronic housing - UM108-SEFE/L-A60 - 2959722



Side element, with foot, tall version, left-hand, for 60 mm wide U-shaped cover.

---

Electronic housing - UM108-SEPEF/L-A60 - 2906500



Side element with foot, tall design, left-hand, for 60 mm wide U-shaped cover, with PE contact to the DIN rail.

---

Electronic housing - UM108-SEFE/L-A73 - 2959735



Side element, with foot, tall version, left-hand, for 73 mm wide U-shaped cover.

---

Electronic housing - UM108-SEPEF/L-A73 - 2906513



Side element with foot, tall design, left, for 73 mm wide U-shaped cover, with PE contact to the DIN rail.

---

## Electronic housing - UM108-PROFIL 235CM BK - 2909963

### Accessories

Electronic housing - UM108 N-SEFE/L-A73 - 2709367



Side element, with foot, low-profile version, left-hand, for 73 mm wide U-shaped cover.

---

Electronic housing - UM108 N-SEPEF/L-A73 - 2709370



Side element with foot, low-profile design, left, for 73 mm wide U-shaped cover, with PE contact to the DIN rail.

---

Electronic housing - UM108-SE-A60 - 2959748



Side element, without foot, tall version, for 60 mm wide U-shaped cover.

---

Side element - UM108-SE-A73 - 2959751



Side element, without foot, tall version, for 73 mm wide U-shaped cover.

---

Electronic housing - UM108 N-SE-A73 - 2709383



Side element, without foot, low-profile version, for 73 mm wide U-shaped cover.

---

Electronic housing - UM108-FE BK - 2909976

Foot element, 107.5 mm wide, for mounting on NS 32 or NS 35/7.5, below profile housing UM 108.

---

## Electronic housing - UM108-PROFIL 235CM BK - 2909963

### Accessories

Electronic housing - UM108-A/U CM - 2854898

Profile covers, tall version, widths of 60 mm (internal dimension 56 mm) and 73 mm (internal dimension 69 mm) are available. Please note the ordering example and the order key.

---

### Drawings

Dimensioned drawing

