

15 Amp Horizontal Rackmount Outlet Strip *1582 Series*

Front Mounted Receptacles

Features



- Designed for power distribution from the front of the unit.
- 1U horizontal 19" rackmount installation.
- Available with lighted on/off switch or red pilot light to indicate power on.
- Available in ASA 61 grey or black powder coat finish.
- [Click here for our surge protected version.](#)

Specifications

- Heavy duty 14 gauge wire cord - 14/3 SJT type for extreme temperature ranges and integral molded plug.
- Plug types available are NEMA 5-15P straight blade or NEMA L5-15P locking type.
- Includes 15 Amp, 125 VAC circuit breaker to prevent accidental overload.
- 6 outlet models include 2 outlets with extra spacing for clearance of most plug in transformers.
- CSA certified, Standards C22.2 (No. 21-95 and No. 42-99)
- UL recognized, Standard UL1363 - file # E166039



Gallery



Accessories

- Mounting Hardware
- Rail Depth Adapter Kit

Black Finish

On/Off Switch	Light Only	Overall Dimensions			Number of Outlets On Front	Number of Outlets On Rear	Outlet NEMA Type	Rotated Outlets	Cord Length (ft)	Plug Blade Type	NEMA Plug Type	Rack Units
Part No.	Part No.	Height	Width	Depth	Front	On Rear	Type	Outlets	(ft)	Type	Type	Units
1582H6A1BK	1582T6A1BK	1.72	19.00	2.66	6	0	5-15R	No	6	Straight	5-15P	1U
1582H6A1BKRA	1582T6A1BKRA	1.72	19.00	2.66	6	0	5-15R	Yes	6	Straight	5-15P	1U
1582H6B1BK	1582T6B1BK	1.72	19.00	2.66	6	0	5-15R	No	15	Straight	5-15P	1U
1582H6B1BKRA	1582T6B1BKRA	1.72	19.00	2.66	6	0	5-15R	Yes	15	Straight	5-15P	1U
1582H6C1BK	1582T6C1BK	1.72	19.00	2.66	6	0	5-15R	No	6	Locking	L5-15P	1U
1582H6C1BKRA	1582T6C1BKRA	1.72	19.00	2.66	6	0	5-15R	Yes	6	Locking	L5-15P	1U
1582H6D1BK	1582T6D1BK	1.72	19.00	2.66	6	0	5-15R	No	15	Locking	L5-15P	1U
1582H6D1BKRA	1582T6D1BKRA	1.72	19.00	2.66	6	0	5-15R	Yes	15	Locking	L5-15P	1U

Unilluminated On/Off Switch	Unilluminated Light Only	Overall Dimensions			Number of Outlets On Front	Number of Outlets On Rear	Outlet NEMA Type	Rotated Outlets	Cord Length (ft)	Plug Blade Type	NEMA Plug Type	Rack Units
Part No.	Part No.	Height	Width	Depth	On Front	On Rear	Type	Outlets	(ft)	Type	Type	Units
1582H8A1BK	1582T8A1BK	1.72	19.00	2.66	8	0	5-15R	No	6	Straight	5-15P	1U
1582H8B1BK	1582T8B1BK	1.72	19.00	2.66	8	0	5-15R	No	15	Straight	5-15P	1U
1582H8C1BK	1582T8C1BK	1.72	19.00	2.66	8	0	5-15R	No	6	Locking	L5-15P	1U
1582H8D1BK	1582T8D1BK	1.72	19.00	2.66	8	0	5-15R	No	15	Locking	L5-15P	1U

ASA 61 Grey Finish

Unilluminated On/Off Switch	Unilluminated Light Only	Overall Dimensions			Number of Outlets On Front	Number of Outlets On Rear	Outlet NEMA Type	Rotated Outlets	Cord Length (ft)	Plug Blade Type	NEMA Plug Type	Rack Units
Part No.	Part No.	Height	Width	Depth	On Front	On Rear	Type	Outlets	(ft)	Type	Type	Units
1582H6A1	1582T6A1	1.72	19.00	2.66	6	0	5-15R	No	6	Straight	5-15P	1U
1582H6B1	1582T6B1	1.72	19.00	2.66	6	0	5-15R	No	15	Straight	5-15P	1U
1582H6C1	1582T6C1	1.72	19.00	2.66	6	0	5-15R	No	6	Locking	L5-15P	1U
1582H6D1	1582T6D1	1.72	19.00	2.66	6	0	5-15R	No	15	Locking	L5-15P	1U
1582H8A1	1582T8A1	1.72	19.00	2.66	8	0	5-15R	No	6	Straight	5-15P	1U
1582H8B1	1582T8B1	1.72	19.00	2.66	8	0	5-15R	No	15	Straight	5-15P	1U
1582H8C1	1582T8C1	1.72	19.00	2.66	8	0	5-15R	No	6	Locking	L5-15P	1U
1582H8D1	1582T8D1	1.72	19.00	2.66	8	0	5-15R	No	15	Locking	L5-15P	1U

Data subject to change without notice