

### General Information

Extended Product Type:	BJM6
Product ID:	1SNA168519R0000
EAN:	3472591685190
Catalog Description:	BJM6-5 POLES Jumper Bars
Long Description:	BJM6 - Jumper Bars - 5 poles - - 6mm Spacing

### Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

### Ordering

EAN:	3472591685190
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

### Dimensions

Product Net Weight:	10.9 g
---------------------	--------

### Container Information

Package Level 1 Units:	10 piece
Package Level 1 Gross Weight:	0.109 kg
Package Level 1 EAN:	3472591685190
Package Level 2 Units:	700 piece
Package Level 3 Units:	117600 piece

### Additional Information

Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Product Main Type:	BJM
Product Name:	Jumper Bar
Rated Current ( $I_n$ ):	Main Circuit 32 A
Sub-Function:	Assembled jumper bar
Sub-Function 2:	Screw
Suitable For:	M2.5/6.4G.1 M4/6.3G

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
RoHS Information:	1SND230492F0201

### Classifications

ETIM 4.0:	EC000489 - Cross-connector for terminal block
ETIM 5.0:	EC000489 - Cross-connector for terminal block
Object Classification Code:	X

