

LS LED

LS LED 600 10.2W 3000K

0050990



Range features

- Ultra slim cross section
- Silver housing and end-caps
- Integrated switch
- Structured diffuser for even light distribution
- 120° light beam
- LED technology: energy and maintenance savings of up to 75%
- Connect up to 10 fixtures in a row with direct connectors or flexible leads for wider spacing or corner connections
- Main cable with EURO-plug, direct and flexible connectors included
- Stainless steel mounting clips for easy installation included
- Available in 830 Homelight
- IP20 & CLASS II
- Mounting support for 90° tilt mounting supplied



PRODUCT OVERVIEW

Ordering number	0050990
Technology	LED
EAN code	5410288509907
Mount	Ceiling surface
Colour temperature (K)	3000
Voltage (V)	220-240
Colour	Silver mat
Included lamp	Integrated LED
IP rating	20
IK rating	2

LS LED

LS LED 600 10.2W 3000K

0050990

DATA TABLE

General data

Technology	LED
Ordering number	0050990
EAN code	5410288509907
E-number SE	7010480
E-number FI	4273597
Mount	Ceiling surface
Long description	Ultra slim cross section. Silver housing and end-caps. Integrated switch. Structured diffuser for even light distribution. 120° light beam. LED technology: energy and maintenance savings of up to 75%. Connect up to 10 fixtures in a row with direct connectors or flexible leads for wider spacing or corner connections. Main cable with EURO-plug, direct and flexible connectors included. Stainless steel mounting clips for easy installation included. Available in 830 Homelight. IP20 & CLASS II. Mounting support for 90° tilt mounting supplied
Product name	LS LED 600 10.2W 3000K
Control gear availability	Included
Control gear mounting	Integral
Control gear type	Electronic
Environment	Interior
Specific application	Ambient Illumination, Ceiling Voids, Kitchen, Shelves, Shoplighting, Under Cabinet, Workbenches
Sales pack quantity	1

Optical data

Colour temperature (K)	3000
Distribution type	Symmetric

Electrical data

Total power consumption (W)	10.2
Voltage (V)	220-240
Glow wire test	650°C
Leading trailing edge	No
Number of heads	1
Total number of lamps	1

LS LED

LS LED 600 10.2W 3000K

0050990

Physical data


Maximum distance from luminaire (cm)	100
Weight (kg)	0.46
Colour	Silver mat
Lamp included	Yes
Included lamp	Integrated LED
Height (mm)	36
Width (mm)	30
Length (mm)	628
IP rating	20
IK rating	2
Diffuser finish	Mat, Ribbed
Single package dimensions (L x W x H) (cm)	87.00 x 4.30 x 3.50
Outer package dimensions (L x W x H) (cm)	87.00 x 4.30 x 3.50

LS LED

LS LED 600 10.2W 3000K

0050990

TECHNICAL DRAWINGS



ENERGY LABEL

