






LOC	DIST	REVISIONS						
J	—	変更						
P	LTR	DESCRIPTION				DATE	DWN	APVD
	D4	ADDED 1-5174912-2 ECR-08-005948				22APR08	TS	KB



1. APPLICABLE P.C.BOARD THICKNESS 1.6mm
2. RECOMMENDED MOUNTING SCREW: 3mm DIA, 6mm LENGTH (MIN.)
TAPPING SCREW SPECIFIED IN JIS B1115, B1122
(TIGHTENING TORQUE : 0.39N·m MAX.)
3. THE MATING PLUG HOUSING PART NUMBER; 174909,174910
4. APPLICABLE PRODUCT SPEC No. ; 108-5281
5. ~~CIRCUIT NUMBER.~~
6. ~~NON INSERTION CIRCUIT NUMBER 21~36~~



1. 適用プリント基板厚：1.6mm
2. 推奨取付ネジ：JIS B1115 , B1122 タッピンネジ, ナベ2種
呼び径3, 長さ6mm以上(締付トルク 0.39N・m)
3. 嵌合相手型番, 174.909, 174.910
4. 適用製品規格番号：108-5281
5. 回路番号(上図参照の事)
6. 端子抜け回路番号 21 ~ 36



プリント基板取付け寸法 (公差±0.1)
(MOUNTING DIMENSIONS FOR P.C.BOARD: TOLERANCE ±0.1)
※ピッチ公差は累積しないこと (NON ACCUMULATE PITCH TOLERANCE)


	—	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 36	全回路 (ALL CIRCUIT)	黒 (BLACK)	1-5174912-2
	SEE DWG 9-174912-2					9-174912-2
OBSOLETE	—	TIN-LEAD	SELECTIVE GOLD × 1	②①	黒 (BLACK)	8-174912-2
	PRE-TIN × 35					
	②① ~ ③⑥	PRE-TIN × 20		—	黒 (BLACK)	7-174912-2
	—	TIN-LEAD	SELECTIVE GOLD × 4	⑩ ⑪ ⑮ ⑯	灰 (GRAY)	6-174912-6
		PRE-TIN × 32				
	—	TIN-LEAD	SELECTIVE GOLD × 2	⑩ ⑪	黒 (BLACK)	5-174912-2
		PRE-TIN × 34				
	—	TIN-LEAD	SELECTIVE GOLD × 4	⑪ ⑫ ⑮ ⑶	黒 (BLACK)	4-174912-2
		PRE-TIN × 32				
	—	TIN-LEAD	SELECTIVE GOLD × 6	⑩ ⑪ ⑫ ⑮ ⑯ ⑶	灰 (GRAY)	3-174912-6
		PRE-TIN × 30				
	—	TIN-LEAD	SELECTIVE GOLD × 5	⑩ ⑪ ⑫ ⑮ ⑯	黒 (BLACK)	2-174912-2
		PRE-TIN × 31				
	—	TIN-LEAD	SELECTIVE GOLD × 36	全回路 (ALL CIRCUIT)	黒 (BLACK)	1-174912-2
	—	PRE-TIN × 36		—	黒 (BLACK)	174912-2
NON INSERTION CIRCUIT NUMBER タブ抜き箇所 ⑥	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	CIRCUIT NO OF GOLD PLATED CONTACT 金めっき端子使用回路番号 ⑤	HOUSING COLOR ハウジング色	PART NUMBER 型番	
	CONTACT FINISH コンタクト仕上げ					

TOLERANCE UNLESS
OTHERWISE SPECIFIED:
一般公差

$0 < x \leq 10$	: ± 0.2
$10 < x \leq 30$	: ± 0.25
$30 < x \leq 100$	: ± 0.3
ANGLE ;	$\pm 3^\circ$

角度

DIMENSIONS:
單位：耗



MATERIAL 材料	HSG: PBT ハウジング: PBT CONTACT: BRASS コンタクト: 黄銅
----------------	---

TOLERANCES UNLESS OTHERWISE SPECIFIED
— 般公差 —

1	PLC	$\pm$	-
2	PLC	$\pm$	-
3	PLC	$\pm$	-
4	PLC	$\pm$	-

FINISH 仕上	SEE TABLE
--------------	-----------

DWN	18MAR04
T.SHINOHARA	
CHK	18MAR04
K.BETSUI	
APVD	18MAR04
K.BETSUI	
PRODUCT SPEC	
製品規格	
SEE NOTE 4	
APPLICATION SPEC	
取付適用規格	
—	
WEIGHT	11.3 g
CUSTOMER DRAWING	

 Tyco Electronics		Tyco Electronics Corporation Kawasaki, Japan	
NAME 名称			
040 SERIES MULTI-LOCK I/O CONNECTOR MK-II 36POSITION CAP HOUSING ASSEMBLY			
SIZE A2	CAGE CODE 00779	DRAWING NO 番号 C-174912	RESTRICTED TO —
SCALE 尺度 2:1		SHEET 1 of 1	REV D4