

Datasheet

Art.No. 91.921.3053.0

Female connector with strain relief GST15i2S B1 ZR1W WS

Connector GST15i2, 2 pole, female, screw connection, 250V/16A, color of coding: white, color of housing: white



Art.No.	91.921.3053.0
EAN	4015573915961
Order unit	1 pieces

Approvals



Technical data

General

Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Strain relief	Yes
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	White
Marking of poles	L, N
Color of housing inclusive strain relief	White

Connection Data

Cable diameter	7.7 mm
Cable diameter 2	6 mm
Connection cross section solid	1.5 mm ²
Cross section solid 2	0.5 mm ²
Connection cross section stranded	1.5 mm ²
Cross section stranded 2	0.5 mm ²
Terminations per pole	1

Model

Model	female
Number of poles	2

Connection type	Screw connection
Degree of protection (IP)	IP20

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	53.2 mm
Width	17.7 mm
Height	13.8 mm

