

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

31067-1070

Status:

Active

Overview:

H-DAC 64™ Unsealed Connector System

Description:

2.54mm H-DAC 64™, 3 Way Male Housing Assembly, Single Row, Polarization A, with Xmas Tree Attachment



Series

image - Reference only

Documents:

- 3D Model

Application Specification AS-31067-100 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-34646-001 (PDF)

General

Product Family	Crimp Housings
Series	31067
Application	Power, Wire-to-Board
Comments	Polarization Option A, Black
Overview	H-DAC 64™ Unsealed Connector System
Product Name	H-DAC 64™
UPC	800756062662

Physical

Circuits (maximum)	3
Circuits Detail	3
Color - Resin	Black
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene, Polyester
Net Weight	2.044/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +100°C

Electrical

Current - Maximum per Contact	11A, 9A
-------------------------------	---------

Material Info

Reference - Drawing Numbers

Application Specification	AS-31067-100
Product Specification	PS-34646-001
Sales Drawing	SD-31110-003

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

31067Series

Mates With

31101 HDAC 64™ Vertical Header

Use With

See Product Spec

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION