

LED LENSER® P7.2 Kit

This accessory set combines LED Lenser's best-selling P7.2 hand torch with a Pressure Sensitive Switch and Gun Mount, making it ideal for any pursuit where hands-free light is needed, including law enforcement, hunting, tracking and camping. The torch itself is a model of lighting efficiency, with first-class performance and durability as you would expect from a German-engineered product. It incorporates Advanced Focus System optics, combining lens and wide internal reflector to provide bright, homogeneous white light from flood to spot beam from a high end CREE LED inside. The single-handed Speed Focus enables light intensity to be changed in a millisecond and can direct 320 lumens up to 260 metres away. At the other end a larger-sized responsive Dynamic Switch is easy to operate even with gloves on and offers three different lighting selections - 'Power', 'Low Power' and 'Boost'. The matt black finish over tough aircraft grade aluminium looks good and allows for a better grip. Power is generated from four AAA batteries on gold-plated contacts that resist corrosion and maximise energy transmission. These batteries provide a maximum burn time of 50 hours. Supplied in a gift box with batteries, mount, pressured switch and torch case.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the-art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Brilliant all-round medium sized torch offering exceptional performance, durability and efficiency
- Kit includes Pressure Sensitive Switch and Gun Mount
- Energy efficient CREE Power+ LED Light Chip
- State-of-the-art, reliable German engineering
- Advanced Focus System™ Optics. Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Dynamic Switch™ - Reactive, large single switch controls light options (Power, Low Power, Boost) and is easier to use with gloves on.
- Speed Focus™ enables smooth single-handed beam focusing
- Recalibrated lens for wider light beam angle
- Robust, yet lightweight aircraft-grade aluminium housing
- User-friendly modular design
- Corrosion resistant gold plated contacts for better conductivity
- Water and dust resistant. IPX54

Technical Information

Size: 130 x 37mm Ø

Power: 320 lumens max

Run Time: up to 50 hours

Beam Distance: up to 260m

Weight: 175grams

Supplied with : Gun Mount, Pressure Switch, Belt Pouch, Wrist-Strap and Duracell® Batteries (4xAAA)

Code	Colour	Packaging	Barcode
1200	Black	Gift Box	4029113tbc