

Datasheet

RS Pro Fused DIN Rail Terminal, CAFL Series, 1000 V, 6.3A, 5 x 20 mm, 5 x 25 mm Fuse, Grey Single

RS Stock No: **796-0867**



Product Details

RS Pro DIN rail deep top hat is made from cold-rolled steel that is zinc coated and clear passivated for corrosion resistance. The coating thickness is a minimum of eight microns. This 35 mm wide symmetric DIN rail top hat is 2000 mm long is compatible with a professional grade TS35 standard DIN rails. The DIN rail top hat is available in full and perforated versions, in various lengths. It measures 2000 x 35 x 15 mm.

Features and Benefits

- Cold rolled steel construction
- Zinc coated and clear passivated
- Available in full and perforated versions, in various lengths
- Meets current BS, DIN and CENELEC standards



Specifications:

Colour	Grey
Current Rating	6.3 A
Fuse Size	5 x 20 mm, 5 x 25 mm
Number of Levels	1
Rail Type Compatibility	DIN32, DIN35, DIN35-15
Termination Method	Screw Clamp
Voltage Rating	1000 V
Wire Size	22 to 10 AWG