

PCB Terminal Blocks

Item Number: 745-811
Marking: MODULAR PCB TERMINAL BLOCK, 2 SOLDER PINS PER POLE WITH JUMPER CAPABILITY
Colour: grey

Product Image

Technical Data

Wiring:	front-entry		
Number of Clamping Units:	1	Number of Clamping Units:	1
Minimum Cross Section [mm ²]:	0.08	max. conductor cross section [mm ²]:	4
Minimum Cross Section [AWG]:	28	max. conductor cross section [AWG]:	12
Pin spacing [mm]:	7.5	Pin spacing [inch]:	0.295
Pin spacing 2 [mm]:		Pin spacing 2 [inch]:	
rated voltage EN [V]:	500	rated voltage UL [V]:	300
rated voltage CSA [V]:		Test Voltage:	
rated search voltage [kV]:	6	Current (Amps.) UL [A]:	10
Current (Amps.) EN [A]:	20	Test Current [A]:	
Current (Amps.) CSA [A]:		Stripped Length [inch]:	0.33
Stripped Length [mm]:	8-9		
Pollution Degree:	3		

