

General Information

Extended Product Type:	BJMI10-3
Product ID:	1SNA176676R0500
EAN:	3472591766769
Catalog Description:	BJMI10-3 POLES Jumper Bars
Long Description:	BJMI10-3 - Jumper Bars - 3 poles - - 10mm Spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

Ordering

EAN:	3472591766769
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	8.00 g
----------------------------	--------

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	155 mm
Package Level 1 Height:	5 mm
Package Level 1 Length:	200 mm
Package Level 1 Gross Weight:	0,08000001 kg
Package Level 1 EAN:	3472591766769
Package Level 2 Units:	1000 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 3 Units:	48000 piece

Additional Information

Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Mounting Type:	Simplified model, composed of a bar prepunched to the spacing of the blocks, and of captive screws and spacers. This accessory can be used for connecting blocks which are consecutive or not: in this case remove the screw and spacer which are not required.

Product Main Type: BJMI
Product Name: Jumper Bar
Rated Current (I_n): Main Circuit 57 A
Spacing: 10 mm
Sub-Function: Assembled jumper bar
Sub-Function 2: Screw

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SND225001C1009
GOST Certificate: 1SND161005A1104
RoHS Information: 1SND230492F0201

Classifications

ETIM 4.0: EC000489 - Cross-connector for terminal block
ETIM 5.0: EC000489 - Cross-connector for terminal block
Object Classification Code: X

